Visit us at Transcat.com!
Visit us at Transcat.com!
Variage Point Drive // Rochester, NY 14624 // Call 1.800.800.5001

NASHCROFT

Sanitary Gauges Type 1032 Accuracy (1.5%-2.0% F.S.)

DESIGNED FOR SAFETY AND LONGER LIFE

- Patented PowerFlex[™] movement isolates movement from shock and vibration for longer life
- All stainless, all-welded construction for long life
- New PLUS! Performance Option:
- Liquid-filled performance in a dry gauge
- Fights vibration and pulsations without liquid-fill headaches
- Autoclavable to 300° F (149° C)
- See page 174 for details
- Order as option XLL
- True Zero™ pointer indication no stop pin to mask false zero reading – ensures safety and process control

OTHER FEATURES:

TRANSCAT

Available in $2^{1/2}$, $3^{1/2}$ and $4^{1/2}$ dial sizes, 1032 sanitary pressure gauges can be autoclaved/sterilized and cleaned or steamed in place (CIP, SIP). These gauges have been designed specifically to meet the needs of the sanitary marketplace.

46

They are available dry, liquid-filled or hermetically sealed to allow for washdowns and *now* with the *PLUS!*[™] performance option.

STANDARD RANGES⁽¹⁾ Pressure Compound/Vacuum psi psi 0/15 30" Hg/0 psi 0/30 30" Hg/15 psi 30" Hg/30 psi 0/60 0/100 30" Hg/60 psi 30" Hg/100 psi 0/160 30" Hg/150 psi 0/200 0/300 30" Hg/300 psi 0/400 0/600 0/1000(2)

1 **1 | S**

⁽¹⁾ Nonstandard ranges available standard including units in bar, kg/cm² and kPa.

⁽²⁾ Consult Tri-Clover, Inc. for appropriate clamps on 1000 psi range.

PRODUCT SPECIFICATIONS

Dial Sizes: 2¹/₂", 3¹/₂" and 4¹/₂" Process Connection: 1¹/₂" and 2" Tri-Clamp* lower and back

Diaphragm and Seal Housing: Electropolished 316L SS (12-20RA Finish)

Case and Ring: 300 series polished stainless steel

Accuracy: 1.5% F.S. for pressure ranges 100 psi thru 600 psi. 2.0% F.S. for vacuum, compound and pressure ranges below 100 psi

Pointer: Adjustable (external zero adjust on $3^{1/2}$ " dial size)

Windows: $2^{1/2}$, $3^{1/2}$ –Polycarbonate standard $4^{1/2}$ –Glass standard

Dial: White with black markings including 3A insignia

Agency Compliance: 3A compliance to standard 74-00 titled – "3A Sanitary Standard for Liquid Pressure and Level sensing Devices"

System Filling: Pharmacuetical/food quality USP grade glycerin (99.5% pure) Optional: Food grade silicone

Optional System Fillings: Consult factory

Case Fillings: The standard sanitary gauge is dry Optional fills include:

Glycerin USP Grade 99.5% pure)
Food grade silicone

Optional Windows: Safety glass and polysulfon $(2^{1}/_{2})^{"}$ and $3^{1}/_{2})^{"}$

Notes:

- (1) 4¹/₂["] available with lower-connect 2["] Tri-Clamp only.
- (2) For other connections, consult the factory.
- (3) Dual scales, metric ranges anfd false reading

dials are available on request. Special dials with colors, logos, etc., available upon request.

| TO ORDER THIS 1032 SANITARY GAUGE: | | | | | |
|--|----|-------|---|-----|---------|
| Select: | 35 | 1032S | L | 15L | 100 psi |
| 1. Dial size-21/2", 31/2" & 41/2" | | | | | |
| 2. Case type–1032 | | | | | |
| 3. Liquid-filled case, if required | | | | | |
| otherwise eliminate | | | | | |
| 4. Process connection Tri-Clamp size-11/2" (15), 2" (20) | | | | | |
| 5. Connection location-Lower (L), Back (B) | | | | | |
| 6. Standard pressure range | | | | | |







Visit us at Transcat.com!